



] PRODUCT DESCRIPTION & TECHNICAL SPECIFICATIONS

Since the SEMIN vapour barrier protective film is applied to all the rafters, the vapour barrier hangers are screwed onto the rafters. To create the plasterboard ceiling, hangers are screwed onto all the vapour protection hangers. The Semin furring (metal framework) is then clipped onto the hangers. The plasterboards can be screwed onto the metal framework. The space thus formed between the vapour barrier and the metal frame is air-tight. It allows all electrical connections, MCV etc. to be passed through this space.

Trade name	Product name	Vapour barrier hanger
Product dimensions	Height (in mm)	78
	Width (in mm)	40
	Length (in mm)	55
	Weight (in kg)	0.06
Material	Galvanised steel	
Consumption	Average consumption (per m ²)	1.8
	Average consumption (per m)	0.6
Install information : all products	Unit pack : type	box
	Unit pack : height (in cm)	5
	Unit pack : width (in cm)	14.5
	Unit pack : depth (in cm)	17.5
	Unit pack : weight (in kg)	3
	Number of products / parcels (in items)	50

] ADVANTAGES

- The vapour barrier is not broken.
- The air tightness system is respected.

] AREA OF APPLICATION

- Creation of a plasterboard ceiling below the vapour barrier protection.
- This allows all electrical connections, MCV etc. to be passed in between the vapour barrier and the metal framework.

] REFERENCES TO TECHNICAL DOCUMENTS

- Customs nomenclature : 73089059

] REFERENCES & PACKAGINGS

- Product reference : A04958
- Barcode : 3585501049583
- Packaging : 50 items per box

] INSTRUCTIONS FOR USE

1. Since the SEMIN vapour protection barrier is applied to all the rafters, the vapour protection hangers are screwed onto the rafters.
2. Then screw the hangers onto all the vapour protection hangers.
3. The Semin furring is then clipped onto the hangers. And the plasterboards can be screwed onto the metal framework.



1.



2.



3.

DO YOU KNOW THE ASSOCIATED SEMIN PRODUCTS ?

- Vapour barrier : The hanger is fixed to it
- Hangers : to insert onto the vapour barrier
- Furring : to clip to the classic hanger